

Catalogue/Datasheet version : October 2008
Reference: C.SD.1000/GB

N°	PROBLEM / PRINTING MISTAKE OR ERROR / NEW INFO	N° PAGE	SOLUTION TO SOLVE THE PROBLEM IN THE NEXT PRINT
1	<p>Following PCN1201001a diffused on 07/07/2009, the following information needs to be updated on the datasheet:</p> <p>Rebound force for N8.4 domes 340g: 110g+/-30g becomes 130g +/-40g</p> <p>Rebound force for N8.4 domes 400g: 110g+/-30g becomes 150g +/-40g</p> <p>Click ratio for N8.4 domes 400g: 60 – 80% becomes 50 – 80%</p> <p>(in case you need a copy of the PCN, please address technic@nicomatic.fr mentioning the above number)</p> <p>N10-4L-400-21/31 :</p>	Back page	<p>Correct in the next edition</p> <p>N10-4L-400-21/31 :</p>
2	<p>The value shown for the life expectancy is incorrect and should be 50 000 activations.</p>	Back page	<p>The value will be replaced on the product datasheet on the next re-print of the documentation.</p>
3	<p>N12 domes with activation force 420g are shown with an older height and travel value.</p>	Back page	<p>Modify the height from 0.80 +/- 0.05 to 0.75 +/- 0.05 and travel from 0.70 +/- 0.05 to 0.65 +/- 0.05</p>

Other mistakes are possible. Do not hesitate to let us know under marketing@nicomatic.fr.